



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



306064 Underground Wire Conn, 60/64, 5 Of Each, 10/Card *Ideal*

Catalog Number	306064
Manufacturer	Ideal
Description	60 64 Undergrd 10 Clam
Weight per unit	0.1950 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Quantity	Card of 10
----------	------------

Material, Color, and Finish

Color	Gray
-------	------

Descriptions

Description	UNDERGROUND WIRE CONN, 60/64, 5 OF EACH, 10/CARD
extra long description	IDEAL 30-6064 60 64 UNDERGRD COMBO,
Features	100% Silicone-based sealant protects against moisture and corrosionUL Listed to 486G Sealed Twist-On Wire Connector for use in damp/wet locations or above-grade applicationsEasy to apply, pre-filled twist-on wire connectorsExpanding, live-action square-wire spring for fast, secure and long-lasting connectionsDeep skirt provides superior moisture resistance to protect connectionsTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)For use in damp/wet location or direct burial/below-grade applications
Long Description	60 64 UNDERGRD 10 CLAM
Product Type	60 64 Undergrd Combo, 10 Clam
Special Features	Smallest wet location/direct burial connector with widest wire range. Non-hardening sealant completely seals out moisture to protect fungus and corrosion. Sealant is stable down to -40° C. Flame-retardant Shell

Manufacturer Information

Brand	Ideal
GTIN	00783250758173
Manufacturers Part Number	30-6064
sub brand	Underground®
UPC	783250758173



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Model 60® & Model 64® Combo Pack

Availability

minimum qty	10
-------------	----

Packaging

Carton	10
Package	50
Weight Per each	0.195

Uses, Certifications, and Standards

Application	Model 60® Handles wire sizes from #20 to #10 AWG copper. Model 60® Minimum of 1 #20 with 1 #18. Model 60® Maximum of 2 #12 & 1 #10 AWG. Model 64® Handles wire sizes from #18 to #8 AWG copper. Model 64® Minimum of 2 #18 AWG. Model 64® Maximum of 2 #10 AWG
standard	UL Listed & CSA certified
Temperature Rating	105