INCANDESCENT	Cat.#		HUBBELL	HUBBELL	
LANABULOU DEDO	Job	Туре		Outdoor Lighting	
LAMI HOLDENO			Approvals		
309					

#### **APPLICATIONS**


 Ideal for a wide variety of industrial and commercial applications as accent and general lighting

### SPECIFICATIONS 309

- Die cast bullet series 175 watt maximum
- 309 Series has extension ring and weathertight lens. Improves shielding and allows universal aiming in wet locations
- Multiple powder paint finishes

#### **LISTINGS**

· Listed to UL1598 for use in wet locations



# **ORDERING INFORMATION**

Catalog Number	Description	Finish	Weight lbs. (kg)			
Wet Location Listed - Universal Aiming <sup>1</sup>						
309-14-ML	9 7/8" long	Matte Black	3 (1.4)			
309-M51-ML	9 7/8" long	Dark Bronze	3 (1.4)			

<sup>1</sup> Use PAR 38 or BR40 lamps, 175w maximum

## **ACCESSORIES - Order Separately**

Catalog Number	Description	
264 0097 9702	Clear lens	.5 (0.2)
1324	Zinc-plated wire guard	.25 (0.1)
309-S	Shield, 7" X 45°, black	1.7 (0.8)
C-5	Wall or tree box, 3 mounting lugs in body; 2 1/2" hubs in "L" shape layout, side access plate	.25 (.11)
S-329-B	Cast round box, 4", 6-sided 1/2" back hub (wall or ceiling)	.75 (.3)
NM-BC	Non-metallic high impact phenolic weatherproof box & cover, box is drilled at 180° for two burial cable connectors (included), allowing feed-through capability; gasketed cover has weathertight 1/2" hub; brass cover with screws; gray	
TRN-XX1	Trunnion adaptor for 1/2" threaded knuckle mount	.5 (.23)

<sup>1</sup> Specify finish, e.g. Dark Bronze - DB



