

Medium Base Lampholder

31528



Medium base, porcelain, screw terminals, keyless, single circuit, fixture pan with 1/8" IPS hickey. White.

features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

specifications

General Info

Type: Incandenscent Medium Base Lampholder

Listing Agencies/Third Party Information

CSA Listing Info: Yes CUL Listing No: No

cULus: No cURus: No Federal Spec: No UL Listing No: Yes UN SPS C: 39111803

UR: No

Dimensions

Diameter Metric: 1.38" Diameter U S: 1.38" Height U S: 2.00"

Technical Information

Volts: 250V Volts A C: 250 Watts: 660

Buy American Act Compliance

Country of Origin: CHINA Buy American Act Status: No