



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



31850 Polyprop Rope 1/2" X 600'

Ideal

Catalog Number	31850
Manufacturer	Ideal
Description	Rope, Polypropylene Material, 600 FT Overall Length, 1/2 In (Rope) Outside Diameter, Rope:Yellow, 3780 LB Tensile Strength, 36.5 LB
Weight per unit	36.5 (lbs/each)
Product Category	Pulling Tools

Features

rope diameter	1/2 IN
---------------	--------

Dimensions and Weight

Length	600 VAC
--------	---------

Descriptions

Description	POLYPROP ROPE 1/2" X 600'
-------------	---------------------------

Manufacturer Information

Brand	IDEAL
GTIN	00783250318506
sub brand	Pro-Pull
UPC	783250318506

Taxonomies, Classifications, and Categories

Category Description	PULL LINE, ROPE, CARRIERS
Type	Rope

Packaging

Carton	1
Weight Per each	36.5

Valu-Line™ Pull-Line

- White with gray tracer for easy identification
- Continuous-fiber polyline great for blowing directly into conduit
- Will not rot or mildew
- Can be left in conduit for future use



Description	Tensile Strength	Cat. No.
Valu-Line™ Pull-Line – 6,500 ft. (bucket)	190 lbs.	31-338

Powr-Fish® Pull-Line

- White with blue tracer for easy identification
- Continuous-fiber polyline great for blowing directly into conduit
- Will not rot or mildew
- Can be left in conduit for future use



Description	Tensile Strength	Cat. No.
Powr-Fish® Pull-Line – 6,500 ft. (bucket)	210 lbs.	31-340
Powr-Fish® Pull-Line – 500 ft. (canister)	210 lbs.	31-348

Powr-Fish® Pull-Line

- White with red tracer for easy identification
- 500 lb. tensile, our highest tensile-rated pull-line
- Continuous-fiber polyline great for blowing directly into conduit
- Will not rot or mildew
- Can be left in conduit for future use



Description	Tensile Strength	Cat. No.
Powr-Fish® Pull-Line – 2,200 ft. (bucket)	500 lbs.	31-344

Pro-Pull™ Rope

- Low-friction polypropylene rope slides easily through conduit
- Non-sliver surface can be handled without gloves
- Will not rot or mildew
- Rugged, lightweight construction



Description	Tensile Strength	Cat. No.
1/4 in. x 250 ft. Reel	1,125 lbs.	31-839
1/4 in. x 600 ft. Reel	1,125 lbs.	31-840
1/4 in. x 1,000 ft. Reel	1,125 lbs.	31-841
3/8 in. x 250 ft. Reel†	2,430 lbs.	31-844
3/8 in. x 600 ft. Reel†	2,430 lbs.	31-845
3/8 in. x 1,200 ft. Reel†	2,430 lbs.	31-846
1/2 in. x 250 ft. Reel†	3,780 lbs.	31-849
1/2 in. x 600 ft. Reel†	3,780 lbs.	31-850
1/2 in. x 1,200 ft. Reel†	3,780 lbs.	31-851
5/8 in. x 600 ft. Reel†	5,580 lbs.	31-853
5/8 in. x 1,200 ft. Reel†	5,580 lbs.	31-854
3/4 in. x 300 ft. Reel†	7,650 lbs.	31-855
3/4 in. x 600 ft. Reel†	7,650 lbs.	31-856
3/4 in. x 1,200 ft. Reel†	7,650 lbs.	31-857

† Eye splice on working end.

3-in-1 Premise MULETAPE®

- Reduces installation time and saves money on premise jobs
- Thread, measure and pull with single product
- Imprinted with sequential footage or meter markings
- Fewer installation steps, significant material and labor savings



THREE functions in ONE

Description	Pulling Strength	Tape Width	Length	Cat. No.
3-in-1 Premise MULETAPE®	400 lb.	1/4 in.	4,500 ft./ bucket	31-314
	1,800 lb.	1/2 in.	1,300 ft./ bucket	31-315

MULETAPE® is a registered trademark of NEPTCO.