



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 3232LA 15A 125V Duplex Recept

*Pass & Seymour/Legrand*

Catalog Number	3232LA
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, #14 to #12 Awg Compatible Wire Size, Grounding Connection, Wall Mount, 1.320 In Length, 0.960 In Width, 3.31 In Height, Thermoplastic, Light Almond, 0.1300 LB
Weight per unit	0.1332 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15 A
connection	Grounding
media	Yes
Poles	2 in
Wire Size	4 in

### Dimensions and Weight

Size	4.2 in
------	--------

### Descriptions

Description	15A 125V DUPLEX RECPT
-------------	-----------------------

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007323221
sub brand	Pass & Seymour
UPC	785007323221

### Taxonomies, Classifications, and Categories

Category Description	Residential recepticals
Type	Straight Blade Receptacle

### Packaging

Carton	10
Package	200
Weight Per each	0.1332

### Uses, Certifications, and Standards

Mounting	WALL
standard	UL 498



## 15A/125V TRADEMASTER® DUPLEX RECEPTACLE, LIGHT ALMOND

3232LA | [Pass & Seymour](#)

### FEATURES & BENEFITS

Our Pass & Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Extra-long strap. Quickloop wire looping aid. Longer tri-drive screws for easier #12 AWG looping.
- Extra-large circuit break-off tabs. Side-access push wire release. Side wire accepts #12 - #14 AWG solid wire. Push wire accepts #14 AWG solid only.
- Low profile face. Traditional contoured face. (3232 models) Self-grounding models provide automatic ground clip.

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Type: Duplex  
Number Of Poles: 2

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42  
CSA Standard: Yes  
cULus: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406

#### DIMENSIONS

Depth (US): .960"  
Height (US): 3.31"

Width (US): 1.32"

#### TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

NEMA Rating: Yes

Volts: 125

Volts (AC): 125

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No