



Pass and Seymour  
Trademaster® 15A 125V Tamper-Resistant Duplex Receptacle, Black  
Part No. 3232TRBK



15A/125A Trademaster® Tamper-Resistant Duplex Receptacle

## Features & Benefits

Quality Materials, durability, and time-tested design

Rated 15 amperes

Wire Size: #12 - #14 AWG, Solid wire

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007240306
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Hospitality, Residential
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty

### Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile      Yes

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Side Only
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 12 AWG
Indoor/Outdoor	Indoor	Wire Connection Type	Push Wire, Screw Terminals
Voltage	125.0 V		