



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



3232TRW 15A 125V Tamper Res Dup Rec

Pass & Seymour/Legrand

Catalog Number	3232TRW
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Duplex Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, #14 to #12 Awg Compatible Wire Size, Grounding Connection, Wall Mount, 1.320 In Length, 1.0 In Width, 3.31 In Height, Thermoplastic, White, Tamper Resistant, Impact Resistant, 0.1300 LB
Weight per unit	0.1329 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15 A
connection	Grounding
media	Yes
Poles	2 in
Wire Size	4 in

Dimensions and Weight

Size	4.2 in
------	--------

Descriptions

Description	15A 125V TAMPER RES DUP REC
-------------	-----------------------------

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007240276
sub brand	Pass & Seymour
UPC	785007240276

Taxonomies, Classifications, and Categories

Category Description	Residential recepticals
Type	Tamper resistant straight blade duplex receptacle

Packaging

Carton	10
Package	1
Weight Per each	0.1329

Uses, Certifications, and Standards

Mounting	WALL
standard	UL 498



15A/125V TRADEMASTER® TAMPER-RESISTANT DUPLEX RECEPTACLE, WHITE

3232TRW | [Pass & Seymour](#)

FEATURES & BENEFITS

Our Pass & Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application. This receptacle is also outfitted with our patented automatic shutter system to prevent young children from inserting common objects, such as hairpins or keys. The shutters release when a plug is inserted. Required by the National Electrical Code® (NEC®).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



PRODUCT
ENVIRONMENTAL PROFILE

- Meets 2008 National Electrical Code Tamper-Resistant requirements.
- Protects children: patented shutter system—now with black "invisi-shutters" that disappear for an invisible effect—helps prevent improper insertion of foreign objects.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Superior protection than traditional outlet caps or protection plates.
- Low profile face.
- Traditional contoured face (3232 models).
- Self-grounding models provide automatic ground clip.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Tamper Resistant
Number Of Poles: 2
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.0"
Height (US): 3.31"
Width (US): 1.320"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 125
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA
Buy American Act Status: No