3232TRW

La legrand[®] designed to be better.

TradeMaster Tamper-Resistant Receptacle

3232TRW



Tamper-Resistant, Duplex Grounding Receptacle. 15 amp, 125 volt. White.

features & benefits

- Meets 2008 National Electrical Code Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Superior protection than traditional outlet caps or protection plates.
- Low profile face.
- Traditional contoured face (3232 models).
- Self-grounding models provide automatic ground clip.

specifications

General Info

Color: White Type: Tamper-Resistant

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42 CSA Standard: Yes cULus: Yes Federal Spec: No UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406

Dimensions

Depth U S: 1" Height U S: 3.31" Width U S: 1.32"

Technical Information

Amps: 15 Amp Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA Buy American Act Status: No