



# 15A/125V WEATHER-RESISTANT DUPLEX RECEPTACLE, BROWN

3232TRWR | Pass & Seymour

#### **FEATURES & BENEFITS**

Whether you need to plug in a hedge trimmer, light a driveway, pathway or deck, or enjoy your favorite music by the pool, our Pass & Seymour weather-resistant receptacles are the better solution. And since this receptacle is tamper resistant as required by the National Electrical Code® (NEC®), you can feel confident that your children will be protected.



- WR markings on face per UL Weather-Resistant requirements.
- Patented internal shutter system lets plugs in, but keeps keys and other objects out with automatic shutters
  that block access
- Side wire accepts #12 #14 AWG solid wire. Push wire accepts #14 AWG solid only.
- Low profile face. Traditional contoured face. High-impact resistant thermoplastic construction.
- Safer and more effective than plastic outlet caps. TR markings identify devices as Tamper-Resistant.
- For covering patents, see www.legrand.us/patents.

## **SPECIFICATIONS**

### **GENERAL INFO**

Color: Brown Type: Duplex Number Of Poles: 2 Number Of Wires: 3

Special Features: Weather-Resistant

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42

CSA Standard: Yes

cULus: Yes

UL Listing No: UL498

UL Standard: Yes UN SPSC: 39121406

## **DIMENSIONS**

Depth (US): 1.0" Height (US): 3.31" Width (US): 1.32"

# **TECHNICAL INFORMATION**

Amps: 15A

NEMA Configuration Number: 5-15R

NEMA Rating: Yes

Volts: 125 Volts (AC): 125

# **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

