

Eaton 32B-BOX

Catalog Number: 32B-BOX

Eaton power device receptacle, Range, #12 - 4 AWG, 50A, Flush, 125/250V, Back, Brown, NEMA 10-50R, Three-pole, Three-wire, Three-pole, three-wire, non grounding, Plug, Glass-filled nylon, Power, Used with S80

General specifications



Photo is representative

Product Name

Eaton power device receptacle

Catalog Number

32B-BOX

UPC

032664198403

Product Length/Depth

8.5 in

Product Height

2.25 in

Product Width

6 in

Product Weight

0.25 lb

Compliances

NAFTA

RoHS Compliant

Certifications

UL Listed

NOM

defaultTaxonomyAttributeLabel

Used with

S80

Special features

Range

Amperage Rating

50 A

Voltage rating

125/250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Three-pole

Color

Brown

Connection type

Plug

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

10-50R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Three-pole, three-wire, non grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 32B-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)