



1 in. Liquidtight Straight Connector, Uninsulated

By Raco
Catalog # 3404



*Representative Image

1 in. Liquidtight Straight Connector, Uninsulated

Features

- Use with flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Innovative split gland-ring assures a perfect seal, preventing pullouts
- Available in trade sizes 3/8 in. through 4 in.
- Sealing washer and heavy-duty locknut included
- All components are reusable

General

Conduit Type	Liquidtight
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Connectors
Insulation Type	Uninsulated
Material	Steel/Malleable Iron
UPC	050169034040

Dimensions

Dimensions	1.938 in x 1.938 in x 2.188 in
Height	2.188 in
Length	1.938 in
Trade Size	1 in
Weight	0.37 lb
Width	1.938 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Division 2• Class II Division 1 & 2• Class III, Division 1 & 2
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	5670

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - LT COND](#)
[Sales Drawings - 3404](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-3404-SPEC-EN | REV 5/2024