

Products

- > [Index](#)
- > [Featured Products](#)
- > [Cross Reference](#)
- > [UPC Search](#)

Product Datasheet

[Catalog Home](#) [Home Page](#)

[Search](#)

3441 -- 45 Degree Liquidtight Connector 3/8" Trade Size



Product Specifications

Family	Liquidtight Conduit and Cord Connectors
Fittings Classification	Malleable Iron - 45 Degree Connectors
Sub Class	Uninsulated
Trade Size	3/8"
Standard Packaging	Carton
Ship Carton Length	7.375
Ship Carton Width	5.375
Ship Carton Height	3.875
WT. PER HU.	20.40
Dimension A	1-3/16"
Dimension B	17/32"
Thread Spec. B	1/2-14 NPT
Dimension C	2-3/8"
Dimension D	1-1/32"
Unit Carton Quantity	25
Ship Carton Quantity	25
UPC Number	050169034415

Applications

- For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit
- Use to positively bond the conduit to a box or enclosure
- RACO® liquidtight connectors are suitable for use in Class 1, Division 2; Class 2, Division 1 and 2; and Class 3, Division 1 and 2 hazardous locations

Product Features

- Patented split gland-ring is designed to slip onto the conduit quickly and to grip the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts
- Malleable iron castings mate with other components perfectly without strain or distortion
- All components are reusable -- RACO® liquidtight connectors may be easily disassembled and reused after years of service
- Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening
- Heavy duty locknut included with every RACO® liquidtight connector assures continuity of ground
- All metallic components are zinc electro plated for added corrosion protection

Compliances

UL CSA

