



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3942 Automation Way
80525-0000, CO Fort Collins
Phone: 970-305-3593
Fax: 970-372-1731



35200 Speed-Driver, 3/16 X 6" *Ideal*

Catalog Number	35200
Manufacturer	Ideal
Description	Quick-Rotating Screwdriver, Chrome Vanadium Steel Blade Material, 3/16 Tip Size, Cabinet Tip Style, Nickel-Chrome Plated, 8-3/4 In Overall Length, 6 In Shank Length, 0.23 LB
Weight per unit	0.2333 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Type	Cushioned Rubber Grip
Shank Length	6
Tip Size	3/16
tip type	Cabinet

Descriptions

Description	SPEED-DRIVER, 3/16 X 6"
Features	The Cabinet Quick Rotating Screwdriver is ideal for threading screws in switches, fixtures and anchors. For quick and easy use, it provides one-handed crank action. It has shank diameter that matches blade tip for tough applications and features a cross-ground tip to provide a precise and secure fit in the screw slot. Plate chipping is prevented by a vapor-blasted tip, and the screwdriver's nickel-chrome plating offers corrosion resistance and a smooth feel. The Cabinet Quick Rotating Screwdriver also feat

Manufacturer Information

Brand	Ideal
GTIN	00783250352005
UPC	783250352005

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Quick-Rotating

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	0.2333

Uses, Certifications, and Standards

Application	For Threading Screws In Switches, Fixtures And Anchors
-------------	--