

T[®]-Cutter Lite Wire Cutter

In today's cutting-edge electronic production and assembly operations, the T[®]-Cutter Lite is a "must-have." Stranded or solid, copper or aluminum, this wire cutter cuts cleanly and accurately.

- Knife-type blade provides a shear-type cut
- Lightweight, compact design
- Perfect for copper and aluminum wire

Description	Cat. No.
T [®] -Cutter Lite Wire Cutter 	45-260

Coax Strip and Crimp Tool

- Precision, form-ground stripping holes remove outer jacket and insulation from RG-59 and RG-6 coaxial cable
- Durable blades cut copper-coated steel conductors
- Three crimping nests for crimping F-connectors and ring terminals



Description	Cat. No.
Coax Strip & Crimp Tool 	30-433
Coax Strip & Crimp Tool w/ten RG-6 F-Connectors	30-433F

Underground Feeder (UF) Cable Stripper

- Self-adjusting stripping blades automatically select proper position
- Strips 12/2 AWG solid to 14/2 AWG Underground Feeder (UF) Cable
- Strips Twin and Earth cable
- Open-throat construction allows unlimited strip length
- Neatly removes outer cable sheath and inner wire sheathing to desired lengths
- Lightweight, ergonomic design reduces user fatigue

Description	Cat. No.
Underground Feeder Cable Stripper 	45-235



Grip-N-Strip™ End Stripper

- Self-adjusting stripping blades automatically select proper position
- Strips 12 AWG solid to 20 AWG stranded PVC insulated wire
- Strip-length gauge
- Cuts up to 12 AWG solid wire
- Lightweight, ergonomic design reduces user fatigue
- Reinforced fiberglass construction
- Hardened steel blades for extra strength and longer life

Description	Cat. No.
Grip-N-Strip™ End Stripper 	45-227

Round Cable Slitting and Ringing Tools


- Cuts around cable jacket as well as slits the length of jacket for easy removal
- Use with single or multiple conductor cable up to 1.75 in. O.D.
- Blade adjusts for jacket thicknesses up to .125 in.
- Spare blade in handle base

Description	Cat. No.
Cable Stripper for 1/4 in. to 3/4 in. O.D. 	45-128
Cable Stripper for 3/4 in. to 1-1/2 in. O.D. 	45-129
Replacement Blades for 45-128 and 45-129 (2/pkg.)	L-7486

Stripmaster[®] Wire Strippers

- One-step stripping enhances productivity
- Spring-action motion increases leverage and reduces operator fatigue
- Precision-ground, knife-type blades provide clean, accurate stripping






Description	Cat. No.
Stripmaster [®] Wire Stripper, 10-22 AWG (Boxed) 	45-092
Stripmaster [®] Wire Stripper, 10-22 AWG (Clamshell)	45-292
Stripmaster [®] Wire Stripper, Coax RG-6	45-262

See Section C for complete Stripmaster[®] Wire Stripper line.

Diagonal-Cutting Pliers

- Drop-forged, high-carbon steel construction withstands toughest applications
- Knife-to-anvil blades never need resharping
- Laser-hardened blades cut hardened wire, bolts and ACSR
- Vinyl-coated, comfort-grip handles for a secure grip
- High-leverage design provides 40% more cutting power
- Models 35-029 and 35-3029 feature a convenient angled head for hard-to-reach areas and rocking out nails



Description (Smart-Grip™ Plier Handles)	Cat. No.
8 in. High-leverage Diagonal 	35-3028
8 in. High-leverage Diagonal w/angled head	35-3029
Description (Dipped Handles)	Cat. No.
8 in. High-leverage Diagonal 	35-028
8 in. High-leverage Diagonal w/angled head 	35-029

Split-Joint Pliers



- Two position slip joints fit large and small jobs
- Dipped comfort-grip handles for a secure grip
- Flush rivet

Description	Cat. No.
6 in. Slip Joint Pliers 	35-100
Description (Dipped Handles)	Cat. No.
8 in. Slip Joint Pliers 	35-102

Multi-Crimp Tools

- Crimps bare or insulated terminals and splices on 10–22 AWG wire
- Knife-to-anvil blades never need resharping
- Excellent leverage for easy crimping and cutting
- Drop-forged, high-carbon steel construction
- Vinyl-coated handles provide a solid, comfortable grip



Description (Smart-Grip™ Plier Handles)	Cat. No.
9-3/4 in. Multi-Crimp Tool 	30-3429
Description (Dipped Handles)	Cat. No.
9-3/4 in. Multi-Crimp Tool 	30-429

Crimp Tool

- Crimps all IDEAL crimp sleeves
- Excellent leverage for right-angle, double-indent crimps
- Cuts and twists wire
- Vinyl-coated handles provide a solid, comfortable grip



Description (Smart-Grip™ Handles)	Cat. No.
10-1/4 in. Crimp Tool 	30-425

Tenite® Grips

- Fits LASERedge™ and WireMan™ Pliers
- Not insulated from electrical shock
- Boil in water to soften for easy installation onto handles



Description	Cat. No.
Replacement grips for 8 in. or 9 in. pliers (one pair)	35-008

Tenite® is a registered trademark of Eastman Chemical Company.

For all your plier needs...



Tongue & Groove



Cable Cutter



Diagonal



Crimper

Side-Cutting Pliers

- Custom chrome vanadium steel for durability
- High leverage pivot requires less cutting force
- Sharp, knife-to-knife blades for easy cutting
- Induction hardened teeth for long life
- Cross-hatched jaws so wires won't slip when pulling
- Ergonomic handles for comfortable, all-day use



Description (Smart-Grip™ Plier Handles)	Cat. No.
9-1/4 in. Side-Cutting Pliers 	35-4012
9-1/4 in. Side-Cutting Pliers w/crimp and fish tape puller 	30-4430
Description (Dipped Handles)	Cat. No.
9-1/4 in. Side-Cutting Pliers 	35-5012
9-1/4 in. Side-Cutting Pliers w/crimp and fish tape puller 	30-5430

Long-Nose Pliers

- Custom chrome vanadium steel for durability
- High leverage pivot requires less cutting force
- Sharp, knife-to-knife blades for easy cutting
- Induction hardened teeth for long life
- Cross-hatched jaws so wires won't slip when pulling
- Ergonomic handles for comfortable, all-day use



Description (Smart-Grip™ Plier Handles)	Cat. No.
6 in. Long-Nose Pliers 	35-4036
8 in. Long-Nose Pliers 	35-4038
Description (Dipped Handles)	Cat. No.
6 in. Long-Nose Pliers 	35-5036
8 in. Long-Nose Pliers 	35-5038

Tongue & Groove Pliers

- Custom chrome vanadium steel for durability
- Ergonomic handles for comfortable, all-day use



Description (Smart-Grip™ Plier Handles)	Cat. No.
10 in. Tongue & Groove Pliers 	35-4430
Description (Dipped Handles)	Cat. No.
10 in. Tongue & Groove Pliers 	35-5430

Cable Cutters

- Custom chrome vanadium steel for durability
- High-leverage pivot requires less force
- Sharp, knife-to-knife blades for easy cutting
- Induction hardened teeth for long life
- Ergonomic handles for comfortable, all-day use



Description (Smart-Grip™ Plier Handles)	Cat. No.
9 in. 2/0 Cable Cutter 	35-4052
Description (Dipped Handles)	Cat. No.
9 in. 2/0 Cable Cutter 	35-5052

Diagonal Cutting Pliers

- Custom chrome vanadium steel for durability
- High leverage pivot requires less cutting force
- Sharp, knife-to-knife blades for easy cutting
- Induction hardened teeth for long life
- Ergonomic handles for comfortable, all-day use



Description (Smart-Grip™ Plier Handles)	Cat. No.
8 in. Diagonal-Cutting Pliers 	35-4028
8 in. Diagonal-Cutting Pliers w/angled head 	35-4029
Description (Dipped Handles)	Cat. No.
8 in. Diagonal-Cutting Pliers 	35-5028
8 in. Diagonal-Cutting Pliers w/angled head 	35-5029

Multi-Crimp Tools

- Custom chrome vanadium steel for durability
- High-leverage pivot requires less force
- Ergonomic handles for comfortable, all-day use
- Cuts, crimps and splices 10 – 22 AWG wire for insulated and non-insulated crimp connectors



Description (Smart-Grip™ Plier Handles)		Cat. No.
9-1/4 in. Multi-Crimp Tool		30-4429
9-1/4 in. Multi-Crimp Tool - Bare Terminals		35-4431
Description (Dipped Handles)		Cat. No.
9-1/4 in. Multi-Crimp Tool		30-5429
9-1/4 in. Multi-Crimp Tool - Bare Terminals		35-5431

IDEAL Grips



LaserEdge™ Dipped Grips

LaserEdge™ Dipped Grips are smooth and easy to wipe clean.

WireMan™ Dipped Grips

WireMan™ Dipped Grips are textured for comfort and control.

Color-coding and FastFinder™ letter markers on SmartGrip™ handles provide quick tool identification, even by touch!



Smart-Grip™

Our Smart-Grip™ pliers provide the latest innovation in material, comfort design, durability and long life.



Side-Cutting



Long Nose



Tongue & Groove



Cable Cutter



Diagonal



Crimper