




Side-Cutting Pliers

- Drop-forged, high-carbon steel construction withstands toughest applications
- Knife-to-anvil blades never need resharpener
- Cuts hardened wire, bolts and ACSR
- Laser-hardened blades and serrated jaws for long-term durability
- High-leverage design provides 40% more cutting power
- Unique reverse rivet protects smooth action of plier movement
- Vinyl-coated, comfort-grip handles for a secure grip



Description (Smart-Grip™ Plier Handles)	Cat. No.
9-1/4 in. New England nose high-leverage w/fish tape puller 	35-3012
9-1/4 in. New England nose high-leverage w/crimping die 	30-3430
Description (Dipped Handles)	Cat. No.
9-1/4 in. New England nose high-leverage w/fish tape puller 	35-012
9-1/4 in. New England nose high-leverage w/crimping die	30-430

Long-Nose Pliers

- Narrow profile head designed for working in tight areas
- Serrated jaws provide secure gripping surface
- Drop-forged, high-carbon steel construction
- Knife-to-anvil blades never need resharpener
- Laser-hardened blades cut hardened wire, bolts and ACSR
- Vinyl-coated, comfort-grip handles for a secure grip



Description (Smart-Grip™ Plier Handles)	Cat. No.
8-1/2 in. Long Nose w/Cutter 	35-3038
Description (Dipped Handles)	Cat. No.
6 in. Long Nose w/Cutter	35-036
7-3/4 in. Long Nose w/Cutter	35-037
8-1/2 in. Long Nose w/Cutter	35-038
8-1/2 in. w/Cutter & stripping holes for 12 & 14 AWG wire 	35-039

Tongue & Groove Pliers

- Patented undercut tongue and groove design ensures solid grip
- Patented reinforced flange protects against breakage
- Laser-hardened teeth remain sharp longer
- Drop-forged, high-carbon steel construction
- Vinyl-coated, comfort-grip handles for a secure grip



Description (Smart-Grip™ Plier Handles)	Jaw Opening (Inches)	Cat. No.
10 in. Tongue & Groove Pliers 	2	35-3430
Description (Dipped Handles)	Jaw Opening (Inches)	Cat. No.
10 in. Tongue & Groove Pliers 	2	35-430
12 in. Tongue & Groove Pliers 	2-1/4	35-440

Cable Cutters

- Drop-forged, high-carbon steel construction
- Precision-ground, hardened cutting edges provide accurate cuts without cable distortion
- Designed for maximum leverage with minimum effort
- Cuts 2/0 copper and 4/0 aluminum (not for use on ACSR)
- Vinyl-coated, comfort-grip handles



Description (Smart-Grip™ Plier Handles)	Cat. No.
9-1/2 in. Cable Cutter 	35-3052
Description (Dipped Handles)	Cat. No.
9-1/2 in. Cable Cutter 	35-052



Side-Cutting



Long Nose

17-Piece Set - #35-809

Set Includes:

- Four LASERedge™ Pliers with Smart-Grip™ Handles (#35-3012 - 9-1/4" Linesman w/fish tape puller, #35-3038 - 8" Long Nose, #35-3430 - 10" Tongue and Groove, #35-3052 - 9-1/2" Cable Cutter)
- #45-915 - Kinetic™ Reflex™ T®-Stripper Wire Stripper
- #35-908 - 7-in-1 Twist-A-Nut™ Screwdriver
- #Five Cushion Grip Screwdrivers (#35-193 - #1 x 3 Phillips, #35-194 - #2 x 4 Phillips, #35-186 - 3/16" x 6 Slotted Cabinet Tip, #35-164 - 1/4" x 4 Slotted round shank, #35-406 - 3/16" x 6 Screw holding slotted)
- #35-286 - Hawkbill Knife
- #35-210 - Electrician's Hammer
- #35-242 - 25' Auto-Lock™ Tape Measure
- #35-205 - Torpedo Level
- #61-086 - Vol-Con® XL Voltage/Continuity Tester
- #35-975 - Tuff-Tote™ Premium Leather Tool Carrier



16 Piece Set - #35-800

Set Includes:

- Five LASERedge™ Pliers with dipped grips (#30-430 - 9-1/4" Linesman w/ crimper, #35-029 - 8" Offset Diagonal, #35-038 - 8" Long Nose, #35-430 - 10" Tongue and Groove, #35-052 - 2/0 Cable Cutter)
- #45-120 - Premium T®-5 T®-Stripper Wire Stripper
- Two Cushion Grip Screwdrivers (#35-194 - #2 x 4 Phillips, #35-164 - 1/4 x 4 Slotted round shank)
- #35-083 - Twist-A-Nut™ Conduit Deburring Tool
- #35-210 - Electrician's Hammer
- #35-242 - 25' Auto-Lock™ Tape Measure
- #35-285 - Electrician's Knife
- #61-086 - Vol-Con® XL Voltage/Continuity Tester
- #61-201 - Replacement battery
- #35-311 - Tuff-Tote™ Leather Tool Pouch
- #35-908 - 7-in-1 Twist-a-Nut™ Screwdriver/Nutdriver



13-Piece Set - #35-790

Set Includes:

- Three LASERedge™ Pliers with Smart-Grip™ handles (#35-3012 - 9-1/4" Linesman w/fish tape puller, #35-3038 - 8" Long Nose, #35-3430 - 10" Tongue and Groove)
- #45-915 - Kinetic™ Reflex™ T®-Stripper Wire Stripper
- Four Cushion Grip Screwdrivers (#35-193 - #1 x 3 Phillips, #35-194 - #2 x 4 Phillips, #35-186 - 3/16" x 4 Slotted Cabinet Tip, #35-164 - 1/4" x 4 Slotted round shank)
- #35-242 - 25' Auto-Lock™ Tape Measure
- #35-286 - Hawkbill Knife
- #34-002 - Medium Size Fuse Puller
- #35-205 - Torpedo Level
- #35-462 - Journeyman Electrician's Tote™



16 Piece Set - #35-808

Set Includes:

- Four LASERedge Pliers with dipped grips (#35-012 - 9-1/4" Linesman w/fish tape puller, #35-038 - 8" Long Nose, #35-430 - 10" Tongue and Groove, #35-012 - 9-1/2" Cable Cutter)
- #45-415 - Reflex™ T®-5 T®-Stripper Wire Stripper
- #30-428 - Combo Crimp/Strip Tool
- Four Cushion Grip Screwdrivers (#35-193 - #1 x 3 Phillips, #35-194 - #2 x 4 Phillips, #35-186 - 3/16" x 6 Slotted Cabinet Tip, #35-164 - 1/4" x 4 Slotted round shank)
- #35-210 - Electrician's Hammer
- #35-242 - 25' Auto-Lock™ Tape Measure
- #34-002 - Pocket Fuse Puller
- #35-286 - Hawkbill knife
- #35-261 - Ergonomic Hacksaw
- #35-427 - 18" Large Mouth Bag

