SNGL HELX SHORT SHIP AUGR 3/4



Features

62° reinforced cutting edge for added durability
Precision ground, self-feeding lead screw
Secondary relief angle for efficient chip removal
Hardened lead screw and cutting edge powers through nails and staples and extends tool life
Hardened & tempered shaft minimizes warping
Quick-change shank design for fast bit changes and use with pneumatic drills
3/4" hole diameter
Overall Length of 7 1/2"
Twist Length of 5"

Models

Description	Catalog #
SNGL HELX SHORT SHIP AUGR 3/4	35-893

©2013 IDEAL INDUSTRIES, INC. All rights reserved.

SNGL HELX SHORT SHIP AUGR 3/4



Features

62° reinforced cutting edge for added durability
Precision ground, self-feeding lead screw
Secondary relief angle for efficient chip removal
Hardened lead screw and cutting edge powers through nails and staples and extends tool life
Hardened & tempered shaft minimizes warping
Quick-change shank design for fast bit changes and use with pneumatic drills
3/4" hole diameter
Overall Length of 7 1/2"
Twist Length of 5"

Models

Description	Catalog #
SNGL HELX SHORT SHIP AUGR 3/4	35-893

©2013 IDEAL INDUSTRIES, INC. All rights reserved.