

Vinyl Electrical Tapes

Scotch® Vinyl Color Coding Electrical Tape 35 (continued)

Order No.	UPC	Color	Length	Width	Thickness	Breaking Strength	Rolls per Carton	Rolls per Case
35-GREEN-3/4	054007-10851	Green	66'	0.75"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-ORANGE-1/2	054007-10273	Orange	20'	0.50"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-ORANGE-3/4	054007-10869	Orange	66'	0.75"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-RED-1/2	054007-10224	Red	20'	0.50"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-RED-3/4	054007-10810	Red	66'	0.75"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-VIOLET-1/2	054007-49923	Violet	20'	0.50"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-VIOLET-3/4	054007-11271	Violet	66'	0.75"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-WHITE-1/2	054007-10232	White	20'	0.50"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-WHITE-3/4	054007-10828	White	66'	0.75"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-YELLOW-1/2	054007-10257	Yellow	20'	0.50"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-YELLOW-3/4	054007-10844	Yellow	66'	0.75"	7 mil	17 lb/in (3.04 kN/m)	10	100
35-MULTI-COLOR	051131-59073	Multi-pack	20'	0.50"	7 mil	17 lb/in (3.04 kN/m)	4	48

Scotch® Vinyl Electrical Tape Super 88

Scotch® Vinyl Electrical Tape Super 88 is a premium grade, 8.5-mil thick, all-weather vinyl insulating tape. It is designed to perform continuously between a temperature range of 0–220°F (-18–105°C). It has an excellent resistance to abrasion, moisture, alkalis, acids, corrosion and varying weather conditions. The combination of elastic backing and aggressive adhesive provides moisture-tight electrical and mechanical protection with minimum bulk. Scotch Tape Super 88 is an Underwriters' Laboratories Listed and Canadian Standards Association Certified "Insulating Tape."

Adhesive Material	Rubber Resin
Backing Material	Polyvinyl Chloride
Tape Grade	Premium
Tape Type	Vinyl
Operating Temperature	0–220°F (-18–105°C)
RoHS 2011/65/EU	Yes
Specifications	ASTM D 3005 type 2, Mil-I- 24391C, VDE 0340 TEIL 3-1, SS 404 09 75

Agency Approvals



Country of Origin



Order No.	UPC	Color	Length	Width	Thickness	Breaking Strength	Rolls per Carton	Rolls per Case
88-SUPER-3/4X66FT	054007-06143	Black	66'	0.75"	8.5 mil	20 lbs/in	10	100
88-SUPER-3/4X44FT	054007-10307	Black	44'	0.75"	8.5 mil	20 lbs/in	10	100
88-SUPER-3/4X36YD	054007-10323	Black	36 yd	0.75"	8.5 mil	20 lbs/in	12	48
88-SUPER-1X36YD	054007-10331	Black	36 yd	1.00"	8.5 mil	20 lbs/in	12	48
88-SUPER-1-1/2X36YD	054007-10349	Black	36 yd	1.50"	8.5 mil	20 lbs/in	-	12
88-SUPER-2X36YD	054007-10356	Black	36 yd	2.00"	8.5 mil	20 lbs/in	-	12
88-SUPER-1-1/2X44FT	054007-10364	Black	44'	1.50"	8.5 mil	20 lbs/in	10	100