



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35T4QCLAX12V 35W 12V Hal GY6.35 Bipin Base Clear Starlite *Sylvania-Ledvance*

Catalog Number	35T4QCLAX12V
Manufacturer	Sylvania-Ledvance
Description	OBS58672 Tungsten Halogen Quartz Bi Pin Starlite Low Pressure Clear Finish Uv Filter With Axial Filament GY6.35 Bi Pin Base 35WATT 12VOLT 4000HR Lamp Life
Weight per unit	0.0200 (lbs/each)
Product Category	Lighting

Features

average life	4000
Base	GY6.35 Bipin
dimnable	Yes
Lamp Type	SINGLE END
lumens	600
Shape	T12
start type	Instant
Voltage Rating	12
Wattage	35

Material, Color, and Finish

color rendering index (cri)	100
color temperature	2900
Finish	Clear

Descriptions

Description	35W 12V HAL GY6.35 BIPIN BASE CLEAR STARLITE
extra long description	SYL 35T4Q/CL/AX-12V/58672 35T4QCLAX
Long Description	OBS58672 Tungsten Halogen Quartz Bi Pin STARLITE Low Pressure Clear Finish UV Filter With Axial Filament GY6.35 Bi Pin Base 35Watt 12Volt 4000Hr Lamp Life
Product Type	35T4QCLAX 12V 40/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135586729
Manufacturers Part Number	35T4Q/CL/AX-12V/58672
sub brand	STARLITE Bi-Pin
UPC	046135586729



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	QUARTZ
Type	HALOGEN

Packaging

Carton	1
Package	40
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Medium Screwbase or bi-pin
-------------	----------------------------