

# Eaton 362412-SD

Catalog Number: 362412-SD

Eaton B-Line series wall mounted panel enclosure,36" height,12" length,24" width,NEMA 4,Hinged cover,SD enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton B-Line series wall mounted panel enclosure	362412-SD
	<b>UPC</b>
	782051092066
<b>Product Length/Depth</b>	<b>Product Height</b>
12 in	36 in
<b>Product Width</b>	<b>Product Weight</b>
24 in	69.2 lb

## Certifications

UL 50  
CSA C22.2.  
NEMA

## defaultTaxonomyAttributeLabel

### Country of origin

US

### Special features

1/4 turn latches

### Style

Medium single door

### Finish color

Painted

### Color

ANSI 61 gray

### NEMA Rating

4

### Cover type

Hinged

### Wall thickness

14 gauge, 14 gauge

### Material

Carbon steel

### Model

SD enclosure

### Mounting method

Wall

### Closure type

Hinged

### Mounting hole details

Thru holes, optional external mounting feet

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 362412-SD](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)