



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



3624812 Encl 36X24X8 N12 Wall MNT SNGL DR CH *Cooper B-Line/Cable Tray*

Catalog Number	3624812
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 36" Height, 8" Length, 24" Width, Nema 12, Hinged Cover, 12 Enclosure, Wall Mount, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	65.5 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	8.0000 IN X 24.0000 IN X 36.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	24.00 In Width X 8.00 In Depth X 36.00 In Height
------	--

Descriptions

Description	ENCL 36X24X8 N12 WALL MNT SNGL DR CH
extra long description	B-LINE 36248-12 TYPE 12 SGL-DOOR EN
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series wall mounted panel enclosure, 36" height, 8" length, 24" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 SGL-Door Enc, 36X24X8
Special Features	Plated door clamps

Manufacturer Information

Brand	Cooper B-Line/Cable Tray
GTIN	00782051801804
Manufacturers Part Number	36248-12
UPC	782051801804

Taxonomies, Classifications, and Categories

Type	Type 12 panel enclosures
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	65.5

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and ControlsCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsOther IT and Datacom - IT and Datacomm - OtherCommercial / Institutional Buildings / Structures - Safety and Security SystemsGeneration - Renewable Energy - Alternative EnergyCommercial / Institutional Buildings / Structures - Critical PowerCommercial / Institutional Buildings / Structures - Building Automation and MonitoringUtility - Substatio
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	UL 508A,CSA C22.2.,NEMA