

Eaton 3764EX

Catalog Number: 3764EX

Eaton locking connector, #10-6 AWG, 50A, Industrial, 600 Vac, 250Vdc, Back wiring, Black, red, Pro grip, Non-NEMA, Three-pole, Four-wire, grounding, Nylon, 0.44 to 1.06 in



General specifications

Product Name	Catalog Number
Eaton Arrow Hart pro grip California standard locking connector	3764EX
	UPC
	032664663772
Product Length/Depth	Product Height
6.94 in	3.38 in
Product Width	Product Weight
3.61 in	1.05 lb
Warranty	Certifications
Refer to warranty document.	cULus Listed
	CSA certified

Product specifications

Special features

Locking connector

Color

Black

Red

Face/body material

Glass filled nylon

Wiring method

Back

Material

Nylon

Allowable wire size

#10-6 AWG

Amperage Rating

50 A

Number Of Poles

Three-pole

Contact material

Zinc plated brass

Type

Locking connector

Device grade

Extra heavy duty

NEMA configuration

Non-NEMA

Design type

Pro grip

Number of wires

Grounding

4

Operating temperature

-40 to 105 °C (-40 to 221 °F)

Voltage rating

600 Vac, 250 Vdc

Cord diameter

0.44-1.06 in (11.1-26.0 mm)

Resources

Catalogs

[Arrow Hart Buyers Guide Section C](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - 3764EX](#)

Application

Industrial

Torque rating

45 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)