

Straight Blade Receptacle 2-Pole 3-Wire 30A 125A



Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007380200
Country Of Origin	China	Number of Receptacles	1
Features	Durable	Outlet Type	Straight Blade
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL listed	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
------------	-----	---------------------	--------

cULus Listed	Yes	CSA File Number	16063
--------------	-----	-----------------	-------

Technical Information

Number of Wires	3	Amperage	30 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	#10 - #6 AWG
-----------------	-------------	-----------	--------------

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-30R
----------------	--------	-------------------------	-------

Voltage	125.0 V
---------	---------

Straight Blade Receptacle 2-Pole 3-Wire 30A 125A



Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007380200
Country Of Origin	China	Number of Receptacles	1
Features	Durable	Outlet Type	Straight Blade
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL listed	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
------------	-----	---------------------	--------

cULus Listed	Yes	CSA File Number	16063
--------------	-----	-----------------	-------

Technical Information

Number of Wires	3	Amperage	30 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	#10 - #6 AWG
-----------------	-------------	-----------	--------------

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-30R
----------------	--------	-------------------------	-------

Voltage	125.0 V
---------	---------
