Pass and Seymour

50A 250V 6-50R Straight Blade Single Flush Receptacle, 2-Pole, 3-Wire

Part No. 3804



Straight Blade Receptacle 2-Pole 3-Wire 50A 250V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007380408
Country Of Origin	China	Number of Receptacles	1
Features	Durable	Outlet Type	Straight Blade
Application Sector	Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
cULus Listed	Yes	CSA File Number	16063

Technical Information

Number of Wires	3	Amperage	50 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	6-50
Wire Connection Type	Screw Terminals	Voltage	250.0 V

Pass and Seymour

50A 250V 6-50R Straight Blade Single Flush Receptacle, 2-Pole, 3-Wire

Part No. 3804



Straight Blade Receptacle 2-Pole 3-Wire 50A 250V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007380408
Country Of Origin	China	Number of Receptacles	1
Features	Durable	Outlet Type	Straight Blade
Application Sector	Multi-Dwelling Unit, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
cULus Listed	Yes	CSA File Number	16063

Technical Information

Number of Wires	3	Amperage	50 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	6-50
Wire Connection Type	Screw Terminals	Voltage	250.0 V