



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



3830 Straight Blade Recp TT30 2P 3W 30A 125V

Pass & Seymour/Legrand

Catalog Number	3830
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Receptacle, 30 A, 125 V, 2 Poles, 3 Wires, Wire Ground Connection, Wall Mount, 2.5 In Length, 1.9 In Width, 3.75 In Height, Thermoplastic, Black, Arc Resistant, 0.3700 LB
Weight per unit	0.3672 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	30
connection	Wire Ground
indoor/outdoor	Indoor
Outlet Type	STRAIGHT BLADE
Poles	3-way
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	10 - 6

Dimensions and Weight

Size	3.8 in
------	--------

Descriptions

Description	STRAIGHT BLADE RECP TT30 2P 3W 30A 125V
extra long description	P&S 3830 STR BLADE RECP TT30 2P 3W

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007790405
UPC	785007790405

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Straight Blade Receptacle

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	25
Weight Per each	0.3672



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Uses, Certifications, and Standards

Mounting

WALL

standard

CULUS, UL, CSA, UL 498