



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106



388 Straight Blade Recp 30A 125/250V 3P 3W

Pass & Seymour/Legrand

Catalog Number	388
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Receptacle, 30 A, 125/250 V Ac, 2 Poles, 3 Wires, Non Ground Connection, Wall Mount, 2.8 In Length, 2.41 In Width, 5.65 In Height, Thermoplastic, Black, Arc Resistant, 1.0800 LB
Weight per unit	1.1 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	30
connection	Non Ground
indoor/outdoor	Indoor
Outlet Type	STRAIGHT BLADE
Poles	3-way
Voltage	125/250 V
Wall Plate Included	NO
Wire Size	4

Dimensions and Weight

Size	5.7 in
------	--------

Descriptions

Description	STRAIGHT BLADE RECP 30A 125/250V 3P 3W
extra long description	P&S 388 STR BLADE RECPT 30A 125/250

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007492200
UPC	785007492200

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Straight Blade Receptacle

Trade Size

Amperage	30.0
----------	------

Packaging

Carton	1
Package	25
Weight Per each	1.0824



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106

Uses, Certifications, and Standards

Mounting	WALL
standard	UL, UL 498