



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 3894 Straight Blade Recp 50A 125/250 3P 4W

*Pass & Seymour/Legrand*

Catalog Number	3894
Manufacturer	Pass & Seymour/Legrand
Description	Blade Receptacle, 50 A, 125/250 V Ac, 3 Poles, 4 Wires, Wire Ground Connection, Wall Mount, 2.5 In Length, 2.2 In Width, 3.75 In Height, Thermoplastic, Black, Arc Resistant, 0.4100 LB
Weight per unit	0.4128 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	50
connection	Wire Ground
indoor/outdoor	Indoor
Outlet Type	STRAIGHT BLADE
Poles	3 Pole
Voltage	125/250 V
Wall Plate Included	NO
Wire Size	10 - 6 (COPPER), UP TO 3 (ALUMINUM)

### Dimensions and Weight

Size	3.8 in
------	--------

### Descriptions

Description	STRAIGHT BLADE RECP 50A 125/250 3P 4W
extra long description	P&S 3894 STR BLADE RECP 50A 125/250

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007807905
UPC	785007807905

### Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Straight Blade Receptacle

### Trade Size

Amperage	50.0
----------	------

### Packaging

Carton	1
Package	25
Weight Per each	0.4128



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Mounting .....	WALL .....
Operating Temperature .....	-40°-75°C .....
standard .....	UL, CULUS, CSA .....