

Eaton 38B-BOX

Catalog Number: 38B-BOX

Eaton power device receptacle, Dryer, #12 - 4 AWG, 30A, Flush, 125/250V, Back, Brown, NEMA 10-30R, Three-pole, Three-wire, Three-pole, three-wire, non grounding, Screw, Glass-filled nylon, Power, Used with S80



Photo is representative

General specifications

| | |
|-------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton power device receptacle | 38B-BOX |
| UPC | Product Length/Depth |
| 032664199103 | 2.226 in |
| Product Height | Product Width |
| 3.674 in | 2.256 in |
| Product Weight | Compliances |
| 0.26 lb | RoHS Compliant |
| | NAFTA |
| Certifications | |
| UL Listed | |

defaultTaxonomyAttributeLabel

Used with

S80

Special features

Dryer

Amperage Rating

30A

Voltage rating

125/250 V

Wiring method

Back

Number of wires

3

Mounting method

Flush

Number Of Poles

Three-pole

Color

Brown

Connection type

Screw

Style

Power

Allowable wire size

#12-4 AWG

NEMA configuration

10-30R

Torque rating

25 lbf-inch

Design type

Receptacle

Material

Glass filled nylon

Receptacle type

Three-pole, three-wire, non grounding

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - 38B-BOX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)