



GE
Lighting

69166 - 38PAR30H/FL25
38PAR30H/FL25



GENERAL CHARACTERISTICS

Lamp Type	Halogen - PAR
Bulb	PAR30
Base	Medium Skirt (E26/50x39)
Filament	CC-8
Rated Life	1500.0 hrs
Bulb Material	Sodalime glass
Primary Application	Indoor Floodlight

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	580.0
Center Beam Candlepower (CBCP)	1750.0
Color Rendering Index (CRI)	100.0
Beam Spread	25.0 °
Nominal Initial Lumens per Watt	15

ELECTRICAL CHARACTERISTICS

Wattage	38.0
Voltage	120.0
Burn Position	Universal

DIMENSIONS

Maximum Overall Length (MOL)	3.6200 in(91.9 mm)
Bulb Diameter (DIA)	3.750 in(95.2 mm)

PRODUCT INFORMATION

Product Code	69166
Description	38PAR30H/FL25
Standard Package	00-Case
Standard Package GTIN	10043168691663
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168691666