

1/2" Duplex E-Z LOCK® Snap-In MC Connector

Bridgeport's ASP line of E-Z LOCK® Duplex Snap-in Connectors offers superior installation speed with no tools required.

To install, push the cables into the rear of the fitting, insert the fitting into the KO at an angle, and rock up to snap the front end in place.

Listed for use with AC / AC90 / ACG90 / MC / MCI-A / HCFMCI-A / MC-PCS Cable*. cETLus Listed.

*See actual listed ranges below.

3939SP (non-insulated) is listed for use cables with 0.54 - 0.73 in. Cable Diameter
 - 10/3 to 8/3 cable AC / AC90 / ACG90 / MC / MCI-A / HCFMCI-A / MC-PCS Cable.

Integral internal spring steel locking tabs fasten cable or conduit. External spring steel locking tabs secures connector to electrical box. Suitable for



*3939SP comes without an insulated throat

[Download Photo](#)



[Download Drawing](#)



[Download Drawing](#)

Product details

Catalog Number:	3939SP
UPC Number:	78174770692
Primary Materials:	Zinc Die Cast
Finish:	Ball Burnished, Mirror Smooth
Trade Size:	1/2"
Unit Quantity:	25
Standard Package Quantity:	100

Dimensions

Trade Size:	1/2"
Dimensions A:	1.855
Dimensions B:	0.458
Dimensions C:	2.022
Dimensions D:	0.622

Certifications & Codes

Federal Specification Number: A-A-50552

UNSPSC: 39121438

Nema Standard: FB-1

UL Standard: Listed ETL Conforms to UL STD 514B Certified to CAN/CSA STD. C22.2 No. 18.3

Patent Number: 7075007