



Powering Business Worldwide

### 3962-BU

Cover 1G Dup Recp Wet Loc Hor Plas GY

UPC: 032664455414

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Straight Blade

Special Features: Angled Body, Grounding

Application: Industrial

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 18 To 12 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Cord Type: 0.25 To 0.69 In Diameter

Material: Polycarbonate

Color: Black, White

NEMA Rating: 5-15P

Connection: Screw

Size: 1.42 In Length X 1.25 In Width X 1.95 In Depth

Environmental Conditions: -40 To 75 Deg C

### 3962W-BU

Cover 1G Dup Recp Wet Loc Hor Plas WH

UPC: 032664543081

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Straight Blade

Special Features: Angled Body, Grounding

Application: Industrial

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 18 To 12 AWG

Amperage Rating: 20 Amp

Voltage Rating: 125 Vac

Cord Type: 0.25 To 0.69 In Diameter

Material: Polycarbonate

Color: Black, White

NEMA Rating: 5-20P

Connection: Screw

Size: 1.51 In Diameter

Environmental Conditions: -40 To 75 Deg C



Powering Business Worldwide

### 3962-BU

Cover 1G Dup Recp Wet Loc Hor Plas GY

UPC: 032664455414

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Straight Blade

Special Features: Angled Body, Grounding

Application: Industrial

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 18 To 12 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Cord Type: 0.25 To 0.69 In Diameter

Material: Polycarbonate

Color: Black, White

NEMA Rating: 5-15P

Connection: Screw

Size: 1.42 In Length X 1.25 In Width X 1.95 In Depth

Environmental Conditions: -40 To 75 Deg C

### 3962W-BU

Cover 1G Dup Recp Wet Loc Hor Plas WH

UPC: 032664543081

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Straight Blade

Special Features: Angled Body, Grounding

Application: Industrial

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 18 To 12 AWG

Amperage Rating: 20 Amp

Voltage Rating: 125 Vac

Cord Type: 0.25 To 0.69 In Diameter

Material: Polycarbonate

Color: Black, White

NEMA Rating: 5-20P

Connection: Screw

Size: 1.51 In Diameter

Environmental Conditions: -40 To 75 Deg C