

# Eaton 3BPS1600RB

Catalog Number: 3BPS1600RB

Eaton pressure switch, 1600A, Copper, NEMA 3R, Underground, Fuse clip: Class L, Four-wire, Three-phase, Used with: 1MM, 3MM, 35MM, 37MM, 35SS and 37SS modular metering stacks, 120/208V, (6) #4 AWG-600 kcmil, Poles: 6



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton pressure switch	3BPS1600RB
<b>UPC</b>	<b>Product Length/Depth</b>
782114350881	25.89 in
<b>Product Height</b>	<b>Product Width</b>
66 in	36 in
<b>Product Weight</b>	<b>Warranty</b>
697 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed	Add suffix ST to catalog number for shunt trip. Fuses not included. 100 kAIC rating on switches with Class L fuses installed. Includes both left and right horizontal bus closure plates.

## defaultTaxonomyAttributeLabel

### Amperage Rating

1600A

### Bus material

Copper

### Feed type

Bottom

### Fuse clip type

Class L

### Phase

Three-phase

### Used with

1MM, 3MM, 35MM, 37MM, 35SS and 37SS modular metering stacks

### Voltage rating

120/208 V

### Wire size

(6) #4 AWG-600 kcmil

### Utility approvals

NC : Dominion

VA : Dominion

MI : DTE Energy (Detroit Edison)

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

### Enclosure

NEMA 3R

### Number of wires

4

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - 3BPS1600RB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)