Eaton 3BR1224L125

Catalog Number: 3BR1224L125

Eaton BR main lug loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, Main lug, 125 A, C1, Aluminum, Cover included, Metallic, 10 kAIC, BR, Combination, NEMA 1,24 Circuits, 12 Spaces, Four-wire, Three-phase, 208 Y/120, 240 V, #6-2/0 AWG Cu/Al

General specifications

Product Name

Eaton BR main lug loadcenter

UPC

786676441407

Product Height

21 in

Product Weight

21 lb

Certifications

UL 67 UL 50

Catalog Number

3BR1224L125

Product Length/Depth

3.88 in

Product Width

14.31 in

Warranty

10 year

Catalog Notes

Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard. Has notch for brhdk125 hold-down kit.



Product specifications

Number of spaces

12

Special features

No feed-thru lugs, includes BREQS125 hold-down screw

Interrupt rating

10 kAIC

Phase

Three-phase

Wire size

#6-2/0 AWG Cu/AI

Bus material

Aluminum

Main circuit breaker

BR

Enclosure

NEMA 1

Amperage Rating

125 A

Mounting

Combination

Enclosure material

Metallic

Type

Main lug

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 1

Number of wires

4

Number of circuits

24

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR

NEMA 1, 120/240 VAC, 3 PHASE

Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR1224L125

Voltage rating

208Y/120, 240V

Box size

C1



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia