

# Eaton 3BR1836L150R

Catalog Number: 3BR1836L150R

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 150 A, C3R, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 36 Circuits, 18 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	3BR1836L150R
<b>UPC</b>	<b>Product Length/Depth</b>
786676441605	5.19 in
<b>Product Height</b>	<b>Product Width</b>
25 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
28.2 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard

## defaultTaxonomyAttributeLabel

### Special features

No feed-thru lugs

### Type

Main lug

### Amperage Rating

150 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Number of circuits

36

### Number of spaces

18

### Phase

Three-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

208Y/120, 240V

### Wire size

#1 AWG-300 kcmil Cu/Al

### Box size

C3R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### NEMA rating

NEMA 3R

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 3 PHASE

### Specifications and datasheets

Eaton Specification Sheet - 3BR1836L150R

3-Phase Loadcenter Program

Number of wires

4



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)