

Eaton 3BR1836L200R

Catalog Number: 3BR1836L200R

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 200 A, C3R, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 36 Circuits, 18 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	3BR1836L200R
UPC	Product Length/Depth
786676442107	5.19 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
28.7 lb	10 year
Certifications	Catalog Notes
UL 67	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard
UL 50	

defaultTaxonomyAttributeLabel

Special features

No feed-thru lugs

Type

Main lug

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

36

Number of spaces

18

Phase

Three-phase

Used with

Type BR 1-inch breakers

Voltage rating

208Y/120, 240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

C3R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

NEMA rating

NEMA 3R

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 3 PHASE

Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR1836L200R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton 3BR1836L200R

Catalog Number: 3BR1836L200R

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 200 A, C3R, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 36 Circuits, 18 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	3BR1836L200R
UPC	Product Length/Depth
786676442107	5.19 in
Product Height	Product Width
21 in	14.31 in
Product Weight	Warranty
28.7 lb	10 year
Certifications	Catalog Notes
UL 67	Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard
UL 50	

defaultTaxonomyAttributeLabel

Special features

No feed-thru lugs

Type

Main lug

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

36

Number of spaces

18

Phase

Three-phase

Used with

Type BR 1-inch breakers

Voltage rating

208Y/120, 240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

C3R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

NEMA rating

NEMA 3R

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 3 PHASE

Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR1836L200R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia