

Eaton 3BR3042B200R

Catalog Number: 3BR3042B200R

Eaton BR main breaker loadcenter, No feed-thru lugs, Main circuit breaker, 200 A, L1r, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, CC, 42 Circuits, 30 Spaces, Four-wire, Three-phase, #1 AWG-250 kcmil Cu/Al, NEMA 3R, 208 Y/120, 240 V



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	3BR3042B200R
UPC	Product Length/Depth
786676440752	3.88 in
Product Height	Product Width
34.13 in	14.31 in
Product Weight	Warranty
23 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached, the maximum rating of the panel is the main breaker rating when used as service entrance equipment.

defaultTaxonomyAttributeLabel

Special features

No feed-thru lugs

Type

Main circuit breaker

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CC

Number of circuits

42

Number of spaces

30

Phase

Three-phase

Wire size

#1 AWG-250 kcmil Cu/Al

Used with

Type BR 1-inch breakers

Voltage rating

208Y/120, 240V

Box size

L1R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

4

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, CC MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 3 PHASE

Specifications and datasheets

Eaton Specification Sheet - 3BR3042B200R

3-Phase Loadcenter Program

NEMA rating

NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia