

# Eaton 3BR3042BC150

Catalog Number: 3BR3042BC150

Eaton BR main breaker loadcenter, Main circuit breaker, 150 A, L1, Copper, NEMA 1, 10 kAIC, CC, 42 Circuits, 30 Spaces, Four-wire, Three-phase, #6-4/0 AWG, NEMA 1



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	3BR3042BC150
<b>UPC</b>	<b>Product Length/Depth</b>
786685883526	39 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
43.34 lb	10 year
<b>Certifications</b>	
UL Listed	

## defaultTaxonomyAttributeLabel

### Type

Main circuit breaker

### Amperage Rating

150 A

### Bus material

Copper

### Main circuit breaker

CC

### Number of circuits

42

### Number of spaces

30

### Phase

Three-phase

### Wire size

#6-4/0 AWG

### Box size

L1

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

### Number of wires

4

### NEMA rating

NEMA 1

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, CC MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 3 PHASE

### Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR3042BC150



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)