

Eaton 3BR3042L200

Catalog Number: 3BR3042L200

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 200 A, G1, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 42 Circuits, 30 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	3BR3042L200
UPC	Product Length/Depth
786676442305	35.75 in
Product Height	Product Width
4.5 in	15.8 in
Product Weight	Warranty
31.4 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

No feed-thru lugs

Type

Main lug

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Mounting

Combination

Number of circuits

42

Number of spaces

30

Phase

Three-phase

Used with

Type BR 1-inch breakers

Voltage rating

208Y/120, 240V

Wire size

#1 AWG-300 kcmil Cu/Al

Box size

G1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR
NEMA 1, 120/240 VAC, 3 PHASE

Specifications and datasheets

Eaton Specification Sheet - 3BR3042L200

3-Phase Loadcenter Program

NEMA rating

NEMA 1

Number of wires

4



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)