

# Eaton 3BR4242B200R

Catalog Number: 3BR4242B200R

Eaton BR main breaker loadcenter, No feed-thru lugs, Main circuit breaker, 200 A, L2r, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, CC, 42 Circuits, 42 Spaces, Four-wire, Three-phase, #1 AWG-250 kcmil Cu/Al, NEMA 3R, 208 Y/120, 240 V

## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	3BR4242B200R
UPC	Product Length/Depth
786676441056	3.88 in
Product Height	Product Width
39 in	14.31 in
Product Weight	Warranty
23 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached, the maximum rating of the panel is the main breaker rating when used as service entrance equipment.



## Product specifications

### Number of spaces

42

### Special features

No feed-thru lugs

### Interrupt rating

10 kAIC

### Phase

Three-phase

### Wire size

#1 AWG-250 kcmil Cu/Al

### Bus material

Aluminum

### Main circuit breaker

CC

### Enclosure

NEMA 3R

### Amperage Rating

200 A

### Enclosure material

Metallic

### Type

Main circuit breaker

### Cover

Cover included

### Used with

Type BR 1-inch breakers

### NEMA rating

NEMA 3R

### Number of wires

4

### Number of circuits

42

### Voltage rating

208Y/120, 240V

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, CC MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 3 PHASE

### Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR4242B200R

Box size

L2R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)