

Eaton 3BR4242L225R

Catalog Number: 3BR4242L225R

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 225 A, L1R, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 42 Circuits, 42 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al

General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	3BR4242L225R
UPC	Product Length/Depth
786676442800	5.19 in
Product Height	Product Width
45 in	14.31 in
Product Weight	Warranty
46 lb	10 year
Certifications	
UL 50 UL 67	

Product specifications

Number of spaces

42

Special features

No feed-thru lugs

Interrupt rating

25 kAIC

Phase

Three-phase

Wire size

#1 AWG-300 kcmil Cu/Al

Bus material

Aluminum

Main circuit breaker

BWH

Enclosure

NEMA 3R

Amperage Rating

225 A

Enclosure material

Metallic

Type

Main lug

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 3R

Number of wires

4

Number of circuits

42

Voltage rating

208Y/120, 240V

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 3 PHASE

Specifications and datasheets

Eaton Specification Sheet - 3BR4242L225R

3-Phase Loadcenter Program

Box size

L1R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)