

Eaton 3MCB1600RBC-600

Catalog Number: 3MCB1600RBC-600

Eaton main circuit breaker, 1600A, Copper, NEMA 3R, Underground, 65 kAIC, RGH, Four-wire, Three-phase, 120/208V, (4) #500-1000 kcmil, With lug landing to accept 2-600M



General specifications

Product Name

Eaton main circuit breaker

Catalog Number

3MCB1600RBC-600

UPC

786685177977

Product Length/Depth

18.5 in

Product Height

57.2 in

Product Width

25.2 in

Product Weight

314 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Amperage Rating

1600 A

Bus material

Copper

Feed type

Bottom

Phase

Three-phase

Voltage rating

120/208 V

Enclosure

NEMA 3R

Interrupt rating

65 kAIC

Accessory/spare part type

Lug landing to accept 2-600M

Main circuit breaker

RGH

Number of wires

4

Wire size

(4) 500-1000 kcmil

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - 3MCB1600RBC-600](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia