

Specifications



Eaton 3MCBE800R

Eaton main circuit breaker, Group Metering, EUSERC, MDL main breaker, 800A, Three-phase, 120/208V, 65 kAIC, Crimp lug landing pads (no lugs included), Four-wire, NEMA 3R enclosure, Aluminum bus, Overhead/underground feed

General specifications

PRODUCT NAME	Eaton main circuit breaker
CATALOG NUMBER	3MCBE800R
UPC	782116136643
PRODUCT LENGTH/DEPTH	11.88 in
PRODUCT HEIGHT	61 in
PRODUCT WIDTH	25.13 in
PRODUCT WEIGHT	170 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	EUSERC Approved
CERTIFICATIONS	UL Listed
CATALOG NOTES	If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].



Powering Business Worldwide

Product specifications

TYPE	EUSERC
AMPERAGE RATING	800 A
BUS MATERIAL	Aluminum
FEED TYPE	Top/bottom
PHASE	Three-phase
VOLTAGE RATING	120/208 V

UTILITY APPROVALS	MI : Consumers Energy ID : Idaho Power OR : Idaho Power WA : Seattle City Light AK : Anchorage Municipal Light & Power NV : NV Energy CA : Pacific Gas and Electric (PG&E) CA : Sacramento Municipal Utility District (SMUD) HI : Hawaiian Electric MT : NorthWestern Energy NE : NorthWestern Energy SD : NorthWestern Energy WY : NorthWestern Energy WA : Puget Sound Energy WA : Tacoma Public Utilities
--------------------------	--

ENCLOSURE	NEMA 3R
INTERRUPT RATING	65 kAIC
MAIN CIRCUIT BREAKER	MDL
NUMBER OF WIRES	4
WIRE SIZE	(6) #1/0 AWG-300 kcmil (3) #1/0 AWG-750 kcmil

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 3MCBE800R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



Specifications



Eaton 3MCBE800R

Eaton main circuit breaker, Group Metering, EUSERC, MDL main breaker, 800A, Three-phase, 120/208V, 65 kAIC, Crimp lug landing pads (no lugs included), Four-wire, NEMA 3R enclosure, Aluminum bus, Overhead/underground feed

General specifications

PRODUCT NAME	Eaton main circuit breaker
CATALOG NUMBER	3MCBE800R
UPC	782116136643
PRODUCT LENGTH/DEPTH	11.88 in
PRODUCT HEIGHT	61 in
PRODUCT WIDTH	25.13 in
PRODUCT WEIGHT	170 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	EUSERC Approved
CERTIFICATIONS	UL Listed
CATALOG NOTES	If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].



Powering Business Worldwide

Product specifications

TYPE	EUSERC
AMPERAGE RATING	800 A
BUS MATERIAL	Aluminum
FEED TYPE	Top/bottom
PHASE	Three-phase
VOLTAGE RATING	120/208 V

UTILITY APPROVALS	MI : Consumers Energy ID : Idaho Power OR : Idaho Power WA : Seattle City Light AK : Anchorage Municipal Light & Power NV : NV Energy CA : Pacific Gas and Electric (PG&E) CA : Sacramento Municipal Utility District (SMUD) HI : Hawaiian Electric MT : NorthWestern Energy NE : NorthWestern Energy SD : NorthWestern Energy WY : NorthWestern Energy WA : Puget Sound Energy WA : Tacoma Public Utilities
--------------------------	--

ENCLOSURE	NEMA 3R
INTERRUPT RATING	65 kAIC
MAIN CIRCUIT BREAKER	MDL
NUMBER OF WIRES	4
WIRE SIZE	(6) #1/0 AWG-300 kcmil (3) #1/0 AWG-750 kcmil

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 3MCBE800R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

