



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



408DCI2 3/4" Ins Diecast Squeeze Connector

Nsi Industries

Catalog Number	408DCI2
Manufacturer	Nsi Industries
Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 3/4 Inch
Weight per unit	0.1290 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	180 Deg
Connector Type	Squeeze, Insulated
Material	Zinc Die Cast
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	3/4
------	-----

Descriptions

Description	3/4" INS DIECAST SQUEEZE CONNECTOR
extra long description	BPT 408-DCI2 3/4" SQUEEZE CONN. INS
Long Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 3/4 Inch
Product Type	3/4" Squeeze Conn. Ins. Zinc
Special Features	Furnished with Tri-Drive screw

Manufacturer Information

Brand	Bridgeport
GTIN	00781747164087
Manufacturers Part Number	408-DCI2
UPC	781747164087

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	3/4
------------	-----

Packaging

Carton	25
Package	100
Weight Per each	0.129



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Used to connect steel flexible metal conduit or XRW FMC to box or enclosure. Insulator rated 105 degree C.

standard

UL

Temperature Rating

105°C