


35156 - 40S11N/1 CARD

GE appliance 40 watt S11 1-pack

- GE's specialty bulbs offer innovative solutions for a variety of lighting needs.
- GE's High Intensity Lights are designed for use in high intensity lamps only.
- 120 volts
- S11 shape with intermediate base for use in appliances
- Whether you're cooking it or keeping it fresh GE appliance lights lets you see it. They're specially designed to withstand high or low temperatures and feature a rugged filament that resists vibration, perfect for microwaves, refrigerators and ovens
- Lasts 500 hours













CAUTIONS & WARNINGS

Warning

- Unexpected lamp rupture may cause injury, fire, or property damage
- Avoid direct water/liquid contact.
- Risk of Fire
- Use in high intensity fixture rated for this product.

GENERAL CHARACTERISTICS

Lamp Type Incandescent - Appliance &

Indicators

Bulb S11

Base Intermediate Screw (E17)

Filament C-9
Bulb Finish Clear
Rated Life 500.0 hrs
Bulb Material Soft glass
Primary Application Appliance

PHOTOMETRIC CHARACTERISTICS

Initial Lumens 440.0 Nominal Initial Lumens per Watt 11

ELECTRICAL CHARACTERISTICS

Wattage 40.0 Voltage 120.0

DIMENSIONS

Maximum Overall Length 2.3100 in(58.7 mm)

(MOL)

Bulb Diameter (DIA) 1.375 in(34.9 mm) Light Center Length (LCL) 1.620 in(41.1 mm)

PRODUCT INFORMATION

Product Code 35156

Description 40S11N/1 CARD

Standard Package Master

Standard Package GTIN 10043168351567

Standard Package Quantity 240
Sales Unit Unit
No Of Items Per Sales Unit 1
No Of Items Per Standard 240

Package

UPC 043168904018