



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1207 Energy Drive
75662-0000, TX Kilgore
Phone: 903-984-8485
Fax: 903-984-8193



410DCI2 1" Ins Diecast Squeeze Connector

Nsi Industries

Catalog Number	410DCI2
Manufacturer	Nsi Industries
Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 1 Inch
Weight per unit	0.2360 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	180 Deg
Connector Type	Squeeze, Insulated
Material	Zinc Die Cast
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	1
------	---

Descriptions

Description	1" INS DIECAST SQUEEZE CONNECTOR
extra long description	BPT 410-DCI2 1 IN Squeeze Conn. Ins
Long Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 1 Inch
Product Type	1 In Squeeze Conn. Ins. Zinc, Box Of 10
Special Features	Furnished with Tri-Drive screw

Manufacturer Information

Brand	Bridgeport
GTIN	00781747164100
Manufacturers Part Number	410-DCI2
UPC	781747164100

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1
------------	---

Packaging

Carton	10
Package	100
Weight Per each	0.236



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1207 Energy Drive
75662-0000, TX Kilgore
Phone: 903-984-8485
Fax: 903-984-8193

Uses, Certifications, and Standards

Application	Used to connect steel flexible metal conduit or XRW FMC to box or enclosure. Insulator rated 105 degree C.
standard	UL
Temperature Rating	105°C