



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 41457 17W Led T8 48" 5K DBL 120-277V 2200LM Glass *Sylvania-Ledvance*

Catalog Number	41457
Manufacturer	Sylvania-Ledvance
Description	4FT, Ledlescenttm Ballast Free Dimmable Led T8, Frosted Glass, 17W, 120 277V, 82 Cri, 2200 Lumens, 5000 K, 50000 HRS Life
Weight per unit	0.4409 (lbs/each)
Product Category	Lighting

### Features

amperage rating	TH
class	PROP65: WARNING: Cancer and Reproductive Harm. This product contains material that, the State of California has determined, may cause cancer <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
Coil Voltage	GB
dimensions	CN
Phase	10.000 5.000

### Descriptions

Description	17W LED T8 48" 5K DBL 120-277V 2200LM GLASS
extra long description	SYL LED17T8/L48/FG/850/BF/41457 LED
Long Description	4ft, LEDlescentTM Ballast Free Dimmable LED T8, frosted glass, 17W, 120 277V, 82 CRI, 2200 Lumens, 5000 K, 50000 hrs Life
Product Type	LED17T8L48FG850BF 25/CS 25/Sku

### Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135414572
Manufacturers Part Number	LED17T8/L48/FG/850/BF/41457
sub brand	Prevail Series
UPC	046135414572

### Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

### Packaging

Carton	1
Package	25
Weight Per each	0.4409

### Uses, Certifications, and Standards

Application	MY
-------------	----