Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

424 4.5" Tongue & Groove

Channellock , Inc.

Catalog Number	424
Manufacturer	Channellock , Inc.
Description	Groove Joint Plier, 0.5 In Cutting Capacity, C1080 High Carbon Steel Cutting Material, Plastic Grip Handle Material, Channellock Blue (Handle), 4.5 In Overall Length, 0.33 In Jaw Length, 0.13 In Jaw Width, 1.26 In Shank Length, 10 Pieces
Weight per unit	0.1200 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Type	CHANNELLOCK BLUE® grips for comfort
Jaw Opening	0.5 in
Material	CHANNELLOCK® uses high-carbon C1080 steel for superior performance on the job and electronic coating for ultimate rust prevention

Dimensions and Weight

Size	4.5" Tongue & Groove

Descriptions

Construction	Patented reinforcing edge minimizes stress breakage
Description	4.5" TONGUE & GROOVE

Manufacturer Information

Brand	CHANNELLOCK
GTIN	00025582301079
UPC	025582301079

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Tongue & Groove, Pump Plier, Water Plier, Tools

Packaging

Carton	1
Package	5
Weight Per each	0.12

Uses, Certifications, and Standards

Application	Mechanical/Home Repair/Auto/Plumbing