



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1612 E. Booth Road
72143-0000, AR Searcy
Phone: 501-368-0309
Fax: 501-368-0619



432LT12 1" Ins Sealtight Straight Diecast Connector

Nsi Industries

Catalog Number	432LT12
Manufacturer	Nsi Industries
Description	Connector, Liquid Tight, Zinc Die Cast, Insulated Throat, Size 1 Inch
Weight per unit	0.4280 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	Straight
Connector Type	Straight, Insulated
Material	Zinc Die Cast
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	1
------	---

Descriptions

Description	1" INS SEALTIGHT STRAIGHT DIECAST CONNECTOR
extra long description	BPT 432-LT12 1 Lqdt. Conn. Ins., Bo
Long Description	Connector, Liquid Tight, Zinc Die Cast, Insulated Throat, Size 1 Inch
Product Type	1 LQDT. Conn. Ins., Box Of 5

Manufacturer Information

Brand	Bridgeport
GTIN	00781747164322
Manufacturers Part Number	432-LT12
UPC	781747164322

Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1
------------	---

Packaging

Carton	5
Package	25
Weight Per each	0.428



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1612 E. Booth Road
72143-0000, AR Searcy
Phone: 501-368-0309
Fax: 501-368-0619

Uses, Certifications, and Standards

Application

Straight connector for use with metallic and non-metallic "Type B" liquid tight conduit. Insulator rated 105 degree C.

standard

UL, CSA