



44026

F96T12 DX/ALTO (PK X 15)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Single Pin (Fa8)

Coating: Copolymer

Color Temperature: 6500 K

Diameter: 1.50 IN

Lamp Type: Fluorescent

Mean Design Lumens: 3950

Package Weight: 22.65 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 75.0 W

Average Life Hours: 12000

Bulb: T12

Color: VIVID

CRI: 84

Initial Lumens: 4500

Length: 96.00 IN

Package (LxWxH): 96.25 IN x 8.75 IN x 5.25 IN

Pack By: 15

Special Features: Shatter-Resistant

UPC: 726585440269

ULEPH,ROHS,NSF Splash Zone