

Eaton 4424 GGV NK

Catalog Number: 4424 GGV NK

Eaton B-Line series wiring trough, 4" height, 24" length, 4" width, GGV NK wireway, Thru holes, No knockouts, Screw cover, NEMA 1, Galvanized steel, Plated screws, Gray, 16 gauge

General specifications



Product Name	Catalog Number
Eaton B-Line series wiring trough	4424 GGV NK
UPC	Product Length/Depth
782051006933	24 in
Product Height	Product Width
4 in	4 in
Product Weight	Certifications
6.619 lb	CSA Certified UL Listed

Material/finish

Material thickness

16 gauge

Finish color

Gray

Model

Closure type

Plated screws

Mounting method

Thru holes

Special features

Cover is secured with plated screws

Type

GGV NK wireway

Resources

Catalogs

[EnviroShield Wireway Flyer](#)

Specifications and datasheets

[Eaton Specification Sheet - 4424 GGV NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)