

Eaton 4424 G NK

Catalog Number: 4424 G NK

Eaton B-Line series wireway, 4" height, 24" length, 4" width, G NK wireway, Thru holes, No knockouts, Screw cover, NEMA 1, Steel, Plated screws, ANSI 61 gray, 16 gauge

General specifications



Product Name	Catalog Number
Eaton B-Line series wireway	4424 G NK
UPC	Product Length/Depth
782051101010	24 in
Product Height	Product Width
4 in	4 in
Product Weight	Certifications
6.619 lb	CSA Certified
	UL Listed

Material/finish

Material thickness

16 gauge

Finish color

ANSI 61 gray

Model

Closure type

Plated screws

Mounting method

Thru holes

Special features

Cover is secured with plated screws

Type

G NK wireway

Resources

Catalogs

[EnviroShield Wireway Flyer](#)

Specifications and datasheets

[Eaton Specification Sheet - 4424 G NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)